






*each interface channel which is not used (card slot without interface card)
has to be equipped with a pullup - resistance, in order to guarantee
a faultless operation of the interfaces*


 *pullup-resistance (47K/0,25W)
with socket (5 pin)*



CHANNEL 2-5



CHANNEL 1



				pullup-resistance for processor card SA2 (in case of interface problems)	Förster Technik GmbH	Zeichnungs-Nr. ski190a	Blatt 1
Darstellung	9.9.99	Ruh			gezeichnet	Datum 28.07.99	Versions-Nr. 1
Änderung	Ind.	Datum	Name		Name Seeger		